

# Digital ABS Plus

Digital ABS Plus™ is designed to simulate standard ABS plastics by combining high-temperature resistance with toughness. Suitable for parts that require PolyJet™ technology's highest possible impact resistance and shock absorption, Digital ABS Plus significantly improves the mechanical performance of parts and prototypes for design verification and functional performance testing.

Get better impact strength with high-temperature resistance, toughness and superior finish.

Digital ABS Plus is ideal for rapid prototyping snap-fit parts for high or low temperature use, functional designs with multi-material versatility and flexibility, molds, manufacturing tools, electrical parts and more.

| Mechanical Properties                                      | Test Method | Objet/J4100/7/8 Series                       | J35/J55                            |
|--|-------------|--|------------------------------------|
| Tensile Strength   | D-638-03    | 55 – 60 MPa<br>(8,000 – 8,700 psi)           | 45-60<br>(6,500-8,700 psi)         |
| Elongation at Break  | D-638-05    | 25 – 40%                                     | 20-35                              |
| Modulus of Elasticity                                      | D-638-04    | 2,600 – 3,000 MPa<br>(375,000 – 435,000 psi) | 2100-2800<br>(305,000-405,000 psi) |
| Flexural Strength  | D-790-03    | 65 – 75 MPa<br>(9,500 – 11,000 psi)          | 55-65<br>(8,000-9,400 psi)         |
| Flexural Modulus   | D-790-04    | 1,700 – 2,200 MPa<br>(245,000 – 320,000 psi) | 1600-1800<br>(230,000-260,000 psi) |
| HDT, oC @ 0.45MPa  | D-648-06    | 58 – 68 °C<br>(136 – 154 °F)                 | 60-65                              |
| HDT, oC @ 0.45MPa after thermal post treatment procedure A | D-648-06    | 82 – 90 °C<br>(180 – 194 °F)                 |                                    |
| HDT, oC @ 0.45MPa after thermal post treatment procedure B | D-648-06    | 92 – 95 °C<br>(198 – 203 °F)                 |                                    |
| HDT, oC @ 1.82MPa  | D-648-07    | 51 – 55 °C<br>(124 – 131 °F)                 |                                    |
| Izod Notched Impact  | D-256-06    | 90 – 115 J/m<br>(1.69 – 2.15 ft lb/in)       | 90-100<br>(1.69-1.87 ft lb/in)     |
| Tg   | DMA, E»     | 47 – 53 °C<br>(117 – 127 °F)                 |                                    |
| Shore Hardness (D)   | Scale D     | 85 – 87 Scale D                              |                                    |
| Rockwell Hardness  | Scale M     | 67 – 69 Scale M                              |                                    |
| Polymerized Density  | ASTM D792   | 1.17 – 1.18 g/cm <sup>3</sup>                |                                    |

# Digital ABS Plus

| System Availability                        | Layer Thickness Capability   | Support Structure   | Available Colors                 |
|--|--|---|----------------------------------|
| Objet260/350/500 Connex3™                  | Digital Material 2/3 mode:<br>30 microns (0.0012 in.)  | SUP705 (WaterJet removable)<br>SUP706B (soluble)                                      | ■ Ivory (RGD515 Plus and RGD531) |
| Objet1000 Plus™                            | Digital Material:<br>34 microns (0.0013 in.)<br>High Speed mode:<br>34 microns (0.0013 in.)<br>High Quality mode:<br>16 microns (0.0006 in.)   | SUP705 (WaterJet removable)   | ■ Ivory (RGD515 Plus and RGD531) |
| Stratasys J735™,<br>Stratasys J750™        | High Mix or High Speed mode:<br>27 microns (0.0011 in.)<br>High Quality mode:<br>14 microns (0.00055 in.)  | SUP705 (WaterJet removable)<br>SUP706B <sup>1</sup> (soluble)                         | ■ Ivory (RGD515 Plus and RGD531) |
| J4100™                                     | Digital Material:<br>27 microns (0.001 in.)  | SUP705 (WaterJet removable)   | ■ Ivory (RGD515 Plus and RGD531) |
| Stratasys J750 Digital Anatomy™            | Horizontal build layers down to<br>14 microns (0.00055 in.)  | SUP705™ (WaterJet removable)<br>SUP706B™ (soluble)<br>GelMatrix™ (WaterJet removable) | ■ Ivory (RGD515 Plus and RGD531) |
| J826™ Prime/J835™/<br>J850™ Pro/J850 Prime | High Speed mode: 27 microns<br>(0.001 in.)<br>High Mix mode: 27 microns<br>(0.001 in.)<br>Super High Quality mode:<br>55 microns (0.002 in.)<br>High Quality mode: 14 microns<br>(0.00055 in.) | SUP705 (WaterJet removable)<br>SUP706B (soluble)                                      | ■ Ivory (RGD515 Plus and RGD531) |
| J55™ Prime                                 | High Quality mode: 18 microns<br>(0.0007 in)   | SUP710™   | ■ Ivory (RGD515 Plus and RGD531) |
| J35™                                       | High Quality mode: 18 microns<br>(0.0007 in)   | SUP710  | ■ Ivory (RGD515 Plus and RGD531) |

1 Not compatible in HQ mode for Stratasys J750.

## USA - Headquarters

7665 Commerce Way  
Eden Prairie, MN 55344, USA  
+1 952 937 3000

## ISRAEL - Headquarters

1 Holtzman St., Science Park  
PO Box 2496  
Rehovot 76124, Israel  
+972 74 745 4000

[stratasys.com](http://stratasys.com)

ISO 9001:2015 Certified

## EMEA

Airport Boulevard B 120  
77836 Rheinmünster, Germany  
+49 7229 7772 0

## ASIA PACIFIC

7th Floor, C-BONS International Center  
108 Wai Yip Street Kwun Tong Kowloon  
Hong Kong, China  
+ 852 3944 8888



**GET IN TOUCH.**

[www.stratasys.com/contact-us/locations](http://www.stratasys.com/contact-us/locations)

